

Spectra-PT Power Tunable Spectral Calibration Sources

Simple uniform sources of luminance and radiance for high dynamic range test and calibration of imaging and non-imaging devices



Speed and accuracy in a simple design

Spectra-PT sources are designed for flat fielding and calibrating cameras and sensors for radiometric responses from low to high light levels. Spectra-PT yields high fidelity measurements while keeping the user experience simple and affordable with turnkey features and excellent dynamic range. A great all-around uniform source system for simple camera and sensor testing.

Spectralon[®], a highly diffuse material inside the sphere, provides stable reflectance and repeatability over the lifetime of the system. The integrating sphere and control electronics are housed in a single enclosure for easy portability, and production ready features such as automation, and easy-to-use software interface with user defined and selectable light levels.

A 13.5 cm integrating sphere with a 5 cm exit port, precision automated variable attenuator, and built in photopic response photodetector allows for continuous adjustability and good dynamic range up to 50,000 cd/m².

The automated VA allows the user to quickly and accurately drive to a preset or selected luminance value. For cameras with wide angle FOV's, Spectra-PT features our WAF (Wide Angle Field Of View) version. Each system comes with a uniformity mapping and National Institute of Standards and Technology (NIST) traceable spectral radiance and luminance calibrations.

Types of test

- Luminance Responsivity
- Image Validation and Correction
- Uniformity
- Flat Fielding

Ideal for calibrating

- CCD and CMOS cameras
- Small area remote sensing devices
- Electronic imaging devices
- Medical endoscopes
- Ambient light sensors
- Security cameras



Specifications and Ordering Information

Model Number: Order Number:

System Performance

Correlated Color Temperature: CCT Est. Luminance Range: cd/m² Est. Equivalent Illuminance at Port: lux Est. Peak Spectral Radiance: µW/cm²-sr-nm @1050 nm Uniformity: Lamp Lifetime: hrs Luminance Attenuator Steps: Dynamic Range/Bits/dB - Full Range of System:

System Components

Sphere Diameter: (ID) Exit Port Diameter: Sphere Coating: Inline Baffle Monitor Detector: Light Source: Detector Response: System Software:

Port Accessories

Standard Aperture Sizes:

System Specifications

Communication: Operating System: Dimensions: (L x W x H) Weight: (approximate)

Included Calibrations (NIST traceable)

Luminance*: Correlated Color Temp: (factory set) Spectral Radiance: (350 - 2400 nm) Spatial Uniformity: *Additional calibrations may be entered by user PT-1000-S AA-01578-001

2856K ± 75K 0 to 50,000 0 to 150,000 180 94% > 500 1.20E+04 4.85E+04/15/93

13.5 cm 5 cm Spectralon® 7.62 cm SD-S1, Silicon Quartz Halogen Photopic & Unfiltered LSS-PT

1.27, 2.54, 3.81 and 5.05 cm

USB 3.0 Windows 10 39 cm x 32 cm x 30 cm 14 kg

cd/m² 2856K at max luminance at max luminance


PT-1000-W AA-01578-000

2800K ± 100K 0 to 50,000 0 to 150,000 180 94% over 180° FOV > 500 1.20E+04 4.85E+04/15/93


13.5 cm 5 cm Dome Spectralon® N/A SD-S1, Silicon Quartz Halogen Photopic & Unfiltered LSS-PT

USB 3.0 Windows 10 39 cm x 32 cm x 30 cm 14 kg

cd/m² 2800K at max luminance at max luminance



Spectra-PT Main Window



Example: PT-1000-S Spectral Radiance at 2856K

